THERMADATA® STAINLESS STEEL PRO LOGGERS

- Integral USB interface for setup & download
- Auto PDF summary
- High temperature range -20 to 125 °C
- 6 probe options available

These ThermaData Stainless Steel Pro loggers are ideal for food, pharmaceutical and other applications where a high temperature data-logger is required. The Stainless Steel Pro is housed in a waterproof, food grade 316 stainless steel case to protect the logger from corrosion, impact and moisture (IP66/67).

The ThermaData Studio software allows the user to programme the logging sample/interval rate (1 second to 255 minutes), the real-time clock, °C/°F, delayed start (maximum 23 hours, 59 minutes), software start, temperature start or time start and a 31-character user ID. The user can also set high and low alarm values for a specific application.

The Stainless Steel Pro is available in five options; without a probe, with a \emptyset 3.3 x 50 mm penetration probe, a \emptyset 4.5 x 100 mm, \emptyset 4.5 x 150 mm, \emptyset 4.5 x 200 mm penetration probe all with a \emptyset 3.3 reduced tip. In addition to the five standard options there is also a \emptyset 1.8 x 20 mm fast response probe variant which is ideal for applications which require a fast ambient reading ie. Dishwashers. Each logger is supplied with a one metre USB-C lead.


THERMADATA STUDIO SOFTWARE & AUTOMATIC PDF FILE OUTPUT

The ThermaData Studio software is supplied as a FREE download. The Stainless Steel Pro logger is connected to a PC via a USB-C port lead and by selecting the relevant icon the data can be downloaded and displayed either as a graph, table or summary. The information can then be analysed by zooming in, saving as a Studio File or exporting to other software packages. The Stainless Steel Pro logger produces a report automatically on computer plug-in, this report will detail high and low alarms and also give you various key information for acceptance for deliveries or processes. No software required to download PDF report.



Example of PDF file

USB connection point Simply unscrew the end cap to access the USB-C connector. Using the supplied USB-C lead this allows the user to connect the logger to a PC and upload any data collected.



MAX/

MIN

.

Order code	Description	
294-900	Stainless steel logger - without probe	
294-940	Stainless steel logger - 20 mm FR probe	
294-930	Stainless steel logger - 50 mm probe	
294-931	Stainless steel logger - 100 mm probe	
294-932	Stainless steel logger - 150 mm probe	
294-933	Stainless steel logger - 200 mm probe	
Supplied with a one metre USB-C lead		

Specification	ThermaData Stainless Steel Pro
Range	-20 to 125 °C
Resolution	0.1 °C
Accuracy	±0.5 °C
Memory	16,000 temperature readings
Sample rate	l second to 255 minutes
Battery	3.6 volt 2/3 AA lithium
Battery life	3 years (based on 6 sec sample rate)
Dimensions	Ø22.5 x 129 mm (excluding probe)
Weight	170 grams - model dependant

IP66/

IP67

HAC